

Advantages

Freely switch wireless and wired operation mode to meet different requirements at the same time.

Two-in-one working mode

Easy to use.



With 2 Individual driving systems, which provide double

2D Technology

protection for the core components. It improves the stability and durability of the device greatly.



New design needle cartridge. Work efficiently

Valve needle cartridge

and stabely with 3 bayonets lock design. Build-in safety isolation zone ensures the sealing performance. More hygienic and safe.

hold with exclusive place.

Special packaging

Convenient storage. Each accessory can be




1-6 speeds, available for different skin types treatment.

LED Screen Visual Digital Display

battery remaining power intuitively. Better control the working hours The pen will turn off automatically after The pen shows "L" when restarting The number of speed flashes slowly 1 minute while the number of speed

A8S with low battery warning helps users to know the



Solve various skin problems Accelerate pigment metabolism, whiten and tender skin, remove acne mark, dilute chloasma and reduce acne pits, improve stretch marks, reduce pores and fine lines.

Before

After




123 mm

The micro-needles reach beyond the epidermis into the dermis, causing pin-point bleeding and tniggering the body's spontaneous healing response.

A8S



After




Product Parameters 119 mm

22 mm

22 mm

52 mm 63 mm



Brand	Dr.pen	Model	A8S		
Power Model	Wired & Wireless	Battery capacity	380mAh		
Speed Level	6 Speeds	Adapter	US/EU/UK/AU/KR		
Needle Adjustment Range	0-2.5mm	G.W.	16.9*12.3*5.6 cm/1 pc/ 373 g		
Handle Material	Metal	1 carton	36*27*33 cm/20 pcs/8 kg		
Available Catridges	12 Pins 18 Pins 24 Pins 36 Pins 42 Pins Nano-S Nano-R		① Вох	② Cable	③ Adapte
Customization (OEM & ODM)	logo, private label, package, new shape,change color.	Packing List	Manual Needle car	⑤ Dr.pen A8S tridge: 18 pins * 2 pcs	6 Batter8 Tray